




Sensor induktif

IS-2002DARKG/US

Produk tidak tersedia - entri arsip



1 L = 150 mm



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	2
Casing	persegi panjang
Dimensi [mm]	28 x 16 x 40

Data kelistrikan

Tegangan pengoperasian [V]	10...55 DC
Pelindung polaritas terbalik	ya

Output


Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	3.7
Arus beban minimal [mA]	4
Kebocoran arus maks. [mA]	0.7
Peringkat arus permanen dari output peralihan DC [mA]	100
Frekuensi peralihan DC [Hz]	1000
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya



Sensor induktif

IS-2002DARKG/US

Zona pendeteksian		
Jangkauan pendeteksian	[mm]	2
Jangkauan pendeteksian real Sr	[mm]	$2 \pm 10 \%$
Jarak pengoperasian	[mm]	0...1.6
Akurasi/deviasi		
Faktor koreksi		baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...60
Perlindungan		IP 65
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing		persegi panjang
Pemasangan		flush mountable
Dimensi	[mm]	28 x 16 x 40
Material		PBT
Elemen display/pengoperasian		
Display	status peralihan	2 x LED, kuning
	operasi	2 x LED, hijau
Keterangan		
Keterangan		torsi pengencangan maks. 0,5 Nm dengan washer
Jumlah paket		1 buah
Koneksi listrik		
Koneksi		



Konektor: 1 x M12