


Sensor induktif

IZB20,8-BROG/V2A

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya tertutup
Jangkauan pendeteksian [mm]	0.8
Casing	berbentuk silinder
Dimensi [mm]	Ø 4 / L = 30

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Pelindung polaritas terbalik	tidak

Output

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya tertutup
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Kebocoran arus maks. [mA]	1
Peringkat arus permanen dari output peralihan DC [mA]	200
Frekuensi peralihan DC [Hz]	2000
Pelindung hubung singkat	tidak
Pelindung beban berlebih	tidak

Zona pendeteksian

Jangkauan pendeteksian [mm]	0.8
Jangkauan pendeteksian real Sr [mm]	0.8 ± 10 %
Jarak pengoperasian [mm]	0...0.65

Akurasi/deviasi

Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2
Histeresis [X01]	1...15
Deviasi titik peralihan [X01]	-10...10

Kondisi pengoperasian



Suhu sekitar [°C]	-25...80
Perlindungan	IP 65



Sensor induktif

IZB20,8-BROG/V2A

Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing	berbentuk silinder	
Pemasangan	flush mountable	
Dimensi	[mm]	Ø 4 / L = 30
Material	baja tahan karat (1.4305/303); POM	
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim	Klem pemasangan: 1	
Keterangan		
Jumlah paket	1 buah	
Koneksi listrik		
Kabel: 2 m, PVC; 3 x 0.14 mm ²		
Koneksi		



BN =
BU =

Warna core :
coklat
biru