


KD5022



Sensor kapasitif

KD-3060-BPKG/NI



Karakteristik produk	
Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	60
Casing	persegi panjang
Dimensi [mm]	120 x 80 x 30
Data kelistrikan	
Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	15; (24 V)
Kelas perlindungan	II
Pelindung polaritas terbalik	ya
Output	
Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	10
Tahan dari hubung singkat	ya
Pelindung beban berlebih	ya
Zona pendeteksian	
Jangkauan pendeteksian [mm]	60
Jangkauan pendeteksian real Sr	60 ± 10 %


KD5022



Sensor kapasitif

KD-3060-BPKG/NI

Jarak pengoperasian	[mm]	0...48.6
Akurasi/deviasi		
Faktor koreksi		kaca: 0.4 / air: 1 / keramik: 0.2 / PVC: 0.2
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-15...15
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...50
Perlindungan		IP 65
Ketahanan yang lebih baik		ya
Pengujian/persetujuan		
EME		EN 60947-5-2
MTTF	[ANN]	615
Data teknis		
Berat	[g]	405
Casing		persegi panjang
Pemasangan		non-flush mountable
Dimensi	[mm]	120 x 80 x 30
Material		PPE dimodifikasi
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		Washer pegas: 4 Sekrup silinder: 4
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 2 m, PVC; 3 x 0.5 mm ²		
Koneksi		



Warna core :
BN = coklat
BK = hitam
BU = biru