


KD5039



Sensor kapasitif

KDE3060-FPKG/NI/US-100-KPF



Karakteristik produk		
Desain kelistrikan		PNP
Fungsi output		biasanya terbuka/biasanya tertutup; (dapat dipilih)
Jangkauan pendeteksian [mm]		60
Casing		persegi panjang
Dimensi [mm]		105 x 80 x 40
Data kelistrikan		
Tegangan pengoperasian [V]		10...36 DC
Konsumsi arus [mA]		5; (24 V)
Kelas perlindungan		II
Pelindung polaritas terbalik		ya
Output		
Desain kelistrikan		PNP
Fungsi output		biasanya terbuka/biasanya tertutup; (dapat dipilih)
Penurunan tegangan maks. pada output peralihan DC [V]		2.5
Peringkat arus permanen dari output peralihan DC [mA]		250
Frekuensi peralihan DC [Hz]		10
Tahan dari hubung singkat		ya
Pelindung beban berlebih		ya
Zona pendeteksian		
Jangkauan pendeteksian [mm]		60



Sensor kapasitif

KDE3060-FPKG/NI/US-100-KPF

Jangkauan pendeteksian real	[mm]	60 ± 10 %	
Sr			
Jarak pengoperasian	[mm]	0...48.6	
Akurasi/deviasi			
Faktor koreksi		kaca: 0.4 / air: 1 / keramik: 0.2 / PVC: 0.2	
Histeresis	[X01]	1...15	
Deviasi titik peralihan	[X01]	-15...15	
Kondisi pengoperasian			
Suhu sekitar	[°C]	-25...80	
Perlindungan		IP 65	
Pengujian/persetujuan			
EME		EN 60947-5-2	
MTTF	[ANN]	537	
Data teknis			
Berat	[g]	309.5	
Casing		persegi panjang	
Pemasangan		non-flush mountable	
Dimensi	[mm]	105 x 80 x 40	
Material		PPE dimodifikasi	
Elemen display/pengoperasian			
Display		status peralihan	1 x LED, kuning
Aksesori			
Item dikirim		Washer pegas: 4	
		Sekrup silinder: 4	
Keterangan			
Jumlah paket		1 buah	

Sensor kapasitif

KDE3060-FPKG/NI/US-100-KPF

Koneksi listrik - colokan

Konektor: 1 x M12; pengkodean: A

