


Sensor kapasitif

KA-3007-BPKG/0,07M/AMP S01

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	7
Casing	berbentuk silinder
Dimensi [mm]	Ø 34

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	1; (24 V)
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	40
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya


KA5009



Sensor kapasitif

KA-3007-BPKG/0,07M/AMP S01

Zona pendeteksian		
Jangkauan pendeteksian	[mm]	7
Kondisi pengoperasian		
Suhu sekitar	[°C]	-15...70
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 60947-5-2	
Data teknis		
Casing		berbentuk silinder
Pemasangan		non-flush mountable
Dimensi	[mm]	Ø 34
Material		PBT
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 2 m, PVC; 3 x 0.5 mm ²		
Koneksi		



BK = Warna core :
 hitam
BN = coklat
BU = biru