


Sensor kapasitif

KB-3020-BPKG/PH

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	3...20
Casing	berbentuk silinder
Dimensi [mm]	Ø 34 / L = 81

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	10; (24 V)
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	40
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian


Jangkauan pendeteksian [mm]	3...20
Jangkauan pendeteksian dapat disesuaikan	ya
Jangkauan pendeteksian pengaturan pabrik [mm]	20
Jangkauan pendeteksian real Sr [mm]	20 ± 10 %
Jarak pengoperasian [mm]	0...16.2



Sensor kapasitif

KB-3020-BPKG/PH

Akurasi/deviasi		
Faktor koreksi	kaca: 0.4 / air: 1 / keramik: 0.2 / PVC: 0.2	
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-15...15
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan	IP 65	
Pengujian/persetujuan		
EME	EN 60947-5-2	
Data teknis		
Casing	berbentuk silinder	
Pemasangan	non-flush mountable	
Dimensi	[mm]	Ø 34 / L = 81
Material	PBT	
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim	Klem pemasangan: 1 obeng: 1	
Keterangan		
Jumlah paket	1 buah	
Koneksi listrik		
Kabel: 2 m, PUR; 3 x 0.5 mm²		
Koneksi		



Warna core :

BN = coklat

BU = biru

BK = hitam