


Sensor kapasitif

KB-3020-APKG/US-100-DPO

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya tertutup
Jangkauan pendeteksian [mm]	20
Casing	berbentuk silinder
Dimensi [mm]	Ø 34

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	< 1
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya tertutup
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	40
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya



Sensor kapasitif

KB-3020-APKG/US-100-DPO

Zona pendeteksian		
Jangkauan pendeteksian	[mm]	20
Jangkauan pendeteksian real Sr	[mm]	20 ± 10 %
Jarak pengoperasian	[mm]	0...16.2
Akurasi/deviasi		
Faktor koreksi		kaca: 0.4 / air: 1 / keramik: 0.2 / PVC: 0.2
Histeresis	[X01]	3...15
Deviasi titik peralihan	[X01]	-15...15
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 65
Pengujian/persetujuan		
EME	EN 60947-5-2	
Data teknis		
Casing		berbentuk silinder
Pemasangan		non-flush mountable
Dimensi	[mm]	Ø 34
Material		PBT
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		Klem pemasangan: 1 obeng: 1
Keterangan		
Jumlah paket		1 buah
Koneksi listrik - colokan		
Konektor: 1 x M12; pengkodean: A		
		

Sensor kapazitif

KB-3020-APKG/US-100-DPO

Koneksi

