

KD5026



Sensor kapasitif

KD-3060-BPKG/NI/6M

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	60
Casing	persegi panjang
Dimensi [mm]	120 x 80 x 30

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	15; (24 V)
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	10
Tahan dari hubung singkat	ya
Pelindung beban berlebih	ya

Zona pendeteksian

Jangkauan pendeteksian [mm]	60
-----------------------------	----

KD5026



Sensor kapasitif

KD-3060-BPKG/NI/6M

Jangkauan pendeteksian real [mm] Sr	60 ± 10 %
Jarak pengoperasian [mm]	0...48.6

Akurasi/deviasi

Faktor koreksi	kaca: 0.4 / air: 1 / keramik: 0.2 / PVC: 0.2
Histeresis [X01]	1...15
Deviasi titik peralihan [X01]	-15...15

Kondisi pengoperasian

Suhu sekitar [°C]	-25...50
Perlindungan	IP 65
Ketahanan yang lebih baik	ya

Pengujian/persetujuan

EME	EN 60947-5-2
MTTF [ANN]	615

Data teknis

Casing	persegi panjang
Pemasangan	non-flush mountable
Dimensi [mm]	120 x 80 x 30
Material	PPE dimodifikasi

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
---------	------------------	-----------------

Aksesori

Item dikirim	obeng: 1
--------------	----------


Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Kabel: 6 m, PVC; 3 x 0.5 mm²

Koneksi



	Warna core :
BN =	coklat
BK =	hitam
BU =	biru