


Sensor kapasitif

KG-3008-BPKG/NI/US



- 1 potensiometer
2 LED



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	8
Casing	tipe berulir
Dimensi [mm]	M18 x 1 / L = 93.8

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	< 10 (24 V DC) / < 15 (36 V DC)
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	50
Tahan dari hubung singkat	ya
Pelindung beban berlebih	ya

Zona pendeteksian

Jangkauan pendeteksian [mm]	8
Jangkauan pendeteksian dapat disesuaikan	ya
Jangkauan pendeteksian pengaturan pabrik [mm]	8
Jangkauan pendeteksian real Sr [mm]	8 ± 10 %
Jarak pengoperasian [mm]	0...6.5



Sensor kapasitif

KG-3008-BPKG/NI/US

Akurasi/deviasi		
Faktor koreksi	kaca: 0.4 / air: 1 / keramik: 0.2 / PVC: 0.2	
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-15...15
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 67
Ketahanan yang lebih baik		ya
Pengujian/persetujuan		
EME	EN 60947-5-2	
MTTF	[ANN]	647
Data teknis		
Berat	[g]	29.4
Casing		tipe berulir
Pemasangan		non-flush mountable
Dimensi	[mm]	M18 x 1 / L = 93.8
Penamaan ulir		M18 x 1
Material		PBT
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim	mur pengunci: 2	
Keterangan		
Jumlah paket	1 buah	
Koneksi listrik - colokan		
Konektor: 1 x M12; pengkodean: A		
		

KG5057

Sensor kapasitif

KG-3008-BPKG/NI/US



Koneksi

