


Sensor kapasitif

KG-2008-FRKG/NI/PH



Karakteristik produk

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka/biasanya tertutup; (dapat dipilih)
Jangkauan pendeteksian [mm]	8
Casing	tipe berulir
Dimensi [mm]	M18 x 1 / L = 84

Data kelistrikan

Tegangan pengoperasian [V]	10...55 DC
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka/biasanya tertutup; (dapat dipilih)
Penurunan tegangan maks. pada output peralihan DC [V]	4.6
Arus beban minimal [mA]	4
Kebocoran arus maks. [mA]	1
Peringkat arus permanen dari output peralihan DC [mA]	250; (400 (...50 °C))
Frekuensi peralihan DC [Hz]	50
Tahan dari hubung singkat	ya
Pelindung beban berlebih	ya

Zona pendeteksian

Jangkauan pendeteksian [mm]	8
Jangkauan pendeteksian dapat disesuaikan	ya
Jangkauan pendeteksian pengaturan pabrik [mm]	8
Jangkauan pendeteksian real Sr [mm]	8 ± 10 %
Jarak pengoperasian [mm]	0...6.5

Akurasi/deviasi

Faktor koreksi	kaca: 0.4 / air: 1 / keramik: 0.2 / PVC: 0.2
Histeresis [X01]	1...15
Deviasi titik peralihan [X01]	-15...15



KG5047



Sensor kapasitif

KG-2008-FRKG/NI/PH

Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 60947-5-2	
MTTF	[ANN]	505
Data teknis		
Berat	[g]	117.5
Casing		tipe berulir
Pemasangan		non-flush mountable
Dimensi	[mm]	M18 x 1 / L = 84
Penamaan ulir		M18 x 1
Material		PBT
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		mur pengunci: 2
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 2 m, PUR / PVC; 2 x 0.34 mm ²		
Koneksi		



BK = Warna core :
WH = hitam
 putih