


KG5066



Sensor kapasitif

KG-3120NFPKGP2T/US



- 1 Ring LED
- 2 tombol pemrograman



Karakteristik produk		
Desain kelistrikan		PNP
Fungsi output		biasanya terbuka/biasanya tertutup; (dapat dipilih)
Jangkauan pendeteksian	[mm]	12
Interface komunikasi		IO-Link
Casing		tipe berulir
Dimensi	[mm]	M18 x 1 / L = 87
Data kelistrikan		
Tegangan pengoperasian	[V]	10...36 DC
Konsumsi arus	[mA]	< 20
Kelas perlindungan		II
Pelindung polaritas terbalik		ya
Prinsip pengukuran		kapasitif
Output		
Desain kelistrikan		PNP
Fungsi output		biasanya terbuka/biasanya tertutup; (dapat dipilih)
Penurunan tegangan maks. pada output peralihan DC	[V]	2.5
Peringkat arus permanen dari output peralihan DC	[mA]	200
Frekuensi peralihan DC	[Hz]	10
Tahan dari hubung singkat		ya
Pelindung beban berlebih		ya
Zona pendeteksian		
Jangkauan pendeteksian	[mm]	12
Akurasi/deviasi		
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-20...20



Sensor kapasitif

KG-3120NFPKGP2T/US

Interface		
Interface komunikasi	IO-Link	
Tipe transmisi	COM1 (4,8 kBaud)	
Revisi O-Link	1.1	
Standar SDCI	IEC 61131-9 CDV	
Profil	Smart Sensor	
Mode SIO	ya	
Waktu siklus proses min. [ms]	101	
DeviceID yang didukung	Tipe operasi	DeviceID
	default	387
Kondisi pengoperasian		
Suhu sekitar [°C]	-25...80	
Catatan tentang suhu sekitar	suhu permukaan pendeteksian: -25...110 °C	
Perlindungan	IP 65; IP 67	
Pengujian/persetujuan		
EME	EN 61000-4-2 ESD	8 kV AD
	EN 61000-4-3 HF dipancarkan	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF dihantarkan	3 V
	EN 55011	kelas B
Ketahanan terhadap getaran	EN 60068-2-6 Fc	(10...55 Hz) / 1 mm amplitudo, periode osilasi 5 menit, 30 menit per sumbu pada resonansi atau 55 Hz
Tahan guncangan	EN 60068-2-27 Ea	30 g 6 guncangan / 11 mdtk setengah sinus (x, y, z)
MTTF [ANN]	662	
Data teknis		
Berat [g]	31.5	
Casing	tipe berulir	
Pemasangan	non-flush mountable	
Dimensi [mm]	M18 x 1 / L = 87	
Penamaan ulir	M18 x 1	
Material	casing: PBT; tombol tekan: TPE-U; Jendela LED: PC	
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Fungsi adaptasi	ya	
Kunci elektronik	ya	
Aksesori		
Item dikirim	mur pengunci: 2	
Keterangan		
Jumlah paket	1 buah	

KG5066



Sensor kapasitif


KG-3120NFPKGP2T/US

Koneksi listrik - colokan

Konektor: 1 x M12; pengkodean: A



Koneksi



4: OUT / IO-Link