


Produk tidak tersedia - entri arsip

**Karakteristik produk**

Fungsi output		biasanya terbuka
Jangkauan pendeteksian	[mm]	10
Casing		tipe berulir
Dimensi	[mm]	M22 x 1

Data kelistrikan

Frekuensi AC	[Hz]	47...63
Tegangan pengoperasian	[V]	20...250 AC/DC
Kelas perlindungan		II

Output

Fungsi output		biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC	[V]	6
Penurunan tegangan maks. pada output peralihan AC	[V]	6
Arus beban minimal	[mA]	4
Kebocoran arus maks.	[mA]	2.0 (250 V AC) / 1.5 (110 V AC) / 0.8 (24 V DC)
Peringkat arus permanen dari output peralihan AC	[mA]	250; (350 (...50 °C))
Peringkat arus permanen dari output peralihan DC	[mA]	100
Frekuensi peralihan AC	[Hz]	25
Frekuensi peralihan DC	[Hz]	50



Sensor kapasitif

SKH-2010-ABOA

Zona pendeteksian		
Jangkauan pendeteksian	[mm]	10
Jangkauan pendeteksian real Sr	[mm]	10 ± 10 %
Jarak pengoperasian	[mm]	0...8.1
Akurasi/deviasi		
Faktor koreksi		kaca: 0.4 / air: 1 / keramik: 0.2 / PVC: 0.2
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-15...15
Kondisi pengoperasian		
Suhu sekitar	[°C]	-15...70
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 60947-5-2	
Data teknis		
Casing		tipe berulir
Pemasangan		non-flush mountable
Dimensi	[mm]	M22 x 1
Penamaan ulir		M22 x 1
Material		kuningan berlapis nikel; PBT
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Koneksi listrik		
Perlindungan yang diperlukan	sekring miniatur sesuai IEC60127-2 lembar 1; ≤ 2 A; cepat	
Keterangan		
Keterangan	Rekomendasi: Periksa keamanan fungsi unit setelah hubung singkat.	
Jumlah paket	1 buah	



Sensor kapasitif

SKH-2010-ABOA

Koneksi listrik

Kabel: 2 m, PVC; 2 x 0.5 mm²

Koneksi



Catatan sekring miniatur sesuai IEC60127-2 lembar 1 ≤ 2 A cepat
Warna core :

BN = coklat
BU = biru