

Sensor kapasitif

KI-3015-BPKG/NI/6M



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	15
Casing	tipe berulir
Dimensi [mm]	M30 x 1.5 / L = 81

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	13; (24 V)
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	40
Tahan dari hubung singkat	ya
Pelindung beban berlebih	ya

Zona pendeteksian

Jangkauan pendeteksian [mm]	15
Jangkauan pendeteksian dapat disesuaikan	ya
Jangkauan pendeteksian pengaturan pabrik [mm]	15
Jangkauan pendeteksian real Sr [mm]	15 ± 10 %
Jarak pengoperasian [mm]	0...12.1

Akurasi/deviasi

Faktor koreksi	kaca: 0.4 / air: 1 / keramik: 0.2 / PVC: 0.2
Histeresis [X01]	1...15



Sensor kapasitif

KI-3015-BPKG/NI/6M

Deviasi titik peralihan	[X01]	-15...15
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...70
Perlindungan		IP 65
Ketahanan yang lebih baik		ya; (Ketahanan yang lebih baik terhadap interferensi frekuensi radio)
Pengujian/persetujuan		
EME	EN 60947-5-2	
MTTF	[ANN]	778
Data teknis		
Berat	[g]	369
Casing		tipe berulir
Pemasangan		non-flush mountable
Dimensi	[mm]	M30 x 1.5 / L = 81
Penamaan ulir		M30 x 1.5
Material		PBT
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		mur pengunci: 2
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 6 m, PVC; 3 x 0.5 mm ²		
Koneksi		



BN = Warna core :
 BU = coklat
 BK = biru
 hitam