


Sensor kapasitif

SKK-3020-ANKG

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	NPN
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	4...20
Casing	tipe berulir
Dimensi [mm]	M38 x 1.5

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	10; (24 V)
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	NPN
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	40
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya



Sensor kapasitif

SKK-3020-ANKG

Zona pendeteksian		
Jangkauan pendeteksian	[mm]	4...20
Jangkauan pendeteksian dapat disesuaikan		ya
Jangkauan pendeteksian pengaturan pabrik	[mm]	20
Jangkauan pendeteksian real Sr	[mm]	20 ± 10 %
Jarak pengoperasian	[mm]	0...16.2
Akurasi/deviasi		
Faktor koreksi		kaca: 0.4 / air: 1 / keramik: 0.2 / PVC: 0.2
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-15...15
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 65
Pengujian/persetujuan		
EME	EN 60947-5-2	
Data teknis		
Casing		tipe berulir
Pemasangan		non-flush mountable
Dimensi	[mm]	M38 x 1.5
Penamaan ulir		M38 x 1.5
Material		kuningan berlapis nikel; PBT
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		mur pengunci: 2 obeng: 1
Keterangan		
Jumlah paket		1 buah

KK7003



Sensor kapasitif

SKK-3020-ANKG

Koneksi listrik

Kabel: 2 m, PVC; 3 x 0.5 mm²

Koneksi



	Warna core :
BK =	hitam
BN =	coklat
BU =	biru