


Sensor kapasitif

KVE4015-CPKG

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	komplementer
Jangkauan pendeteksian [mm]	15
Casing	persegi panjang
Dimensi [mm]	40 x 40 x 118

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	< 20
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	komplementer
Penurunan tegangan maks. pada output peralihan DC [V]	3
Peringkat arus permanen dari output peralihan DC [mA]	200
Frekuensi peralihan DC [Hz]	10
Pelindung hubung singkat	ya



Sensor kapasitif

KVE4015-CPKG

Tipe pelindung hubung singkat		berpulsa	
Pelindung beban berlebih		ya	
Zona pendeteksian			
Jangkauan pendeteksian	[mm]	15	
Jangkauan pendeteksian dapat disesuaikan		ya	
Jangkauan pendeteksian pengaturan pabrik	[mm]	15	
Jangkauan pendeteksian real Sr	[mm]	15 ± 10 %	
Jarak pengoperasian	[mm]	0...12.1	
Akurasi/deviasi			
Faktor koreksi		kaca: 0.4 / air: 1 / keramik: 0.2 / PVC: 0.2	
Histeresis	[X01]	1...15	
Deviasi titik peralihan	[X01]	-15...15	
Kondisi pengoperasian			
Suhu sekitar	[°C]	-25...70	
Perlindungan		IP 65	
Pengujian/persetujuan			
EME		EN 60947-5-2	
Data teknis			
Casing		persegi panjang	
Pemasangan		flush mountable	
Dimensi	[mm]	40 x 40 x 118	
Material		PBT	
Elemen display/pengoperasian			
Display		status peralihan	1 x LED, kuning
		operasi	1 x LED, hijau
Keterangan			
Keterangan		Konektor kabel (E11270) harus dipesan secara terpisah	
Jumlah paket		1 buah	

KV5001



Sensor kapasitif

KVE4015-CPKG

Koneksi listrik

terminal: ...2.5 mm²

Koneksi

