



Sensor silinder T-slot

MKT2028BARKG/G/ZH



- 1 klem pengencang
2 Permukaan pendeteksian



Karakteristik produk		
Desain kelistrikan		PNP/NPN
Fungsi output		biasanya terbuka
Dimensi	[mm]	25 x 5 x 6.5
Data kelistrikan		
Tegangan pengoperasian	[V]	10...30 DC; ("kelas suplai 2" menurut cULus)
Kelas perlindungan		III
Pelindung polaritas terbalik		ya
Waktu penundaan pengaktifan maks.	[ms]	30
Output		
Desain kelistrikan		PNP/NPN
Fungsi output		biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC	[V]	4.5
Arus beban minimal	[mA]	5
Kebocoran arus maks.	[mA]	0.8
Peringkat arus permanen dari output peralihan DC	[mA]	100
Frekuensi peralihan DC	[Hz]	4000
Pelindung hubung singkat		ya
Pelindung beban berlebih		ya
Zona pendeteksian		
Sensitivitas respons	[mT]	2.8
Kecepatan pergerakan	[m/s]	> 10



Sensor silinder T-slot

MKT2028BARKG/G/ZH

Akurasi/deviasi		
Histeresis	[mm]	1.5
Kemampuan pengulangan	[mm]	< 0.2
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...85
Perlindungan		IP 65; IP 67
Pengujian/persetujuan		
EME	EN 61000-4-2 ESD	- CD / 8 kV AD
	EN 61000-4-3 HF dipancarkan	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF dihantarkan	10 V
	EN 55011	kelas B
MTTF	[ANN]	3145
Persetujuan UL	Persetujuan UL no.	C003
Data teknis		
Berat	[g]	26.6
Pemasangan		flush mountable
Tipe pemasangan		klem pengencang dengan slot kombinasi/soket segienam, lebar penampang 1,5
Tipe silinder		Silinder T-slot
Dimensi	[mm]	25 x 5 x 6.5
Material		PA; klem pengencang: baja tahan karat
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		placeholder karet: 1
		Klip kabel: 1
Keterangan		
Jumlah paket		1 buah

MK5103



Sensor silinder T-slot

MKT2028BARKG/G/ZH

Koneksi listrik

Kabel: 2 m, PUR; 2 x 0.14 mm²

Koneksi



BN = Warna core :
BU = coklat
 biru