


MK500A



Sensor silinder T-slot

MKT3028BBPKG/G/ZH/3D



- 1 klem pengencang
2 Permukaan pendeteksian



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Dimensi [mm]	25 x 5 x 6.5

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	< 10
Kelas perlindungan	III
Pelindung polaritas terbalik	ya
Waktu penundaan pengaktifan maks. [ms]	30

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	100
Frekuensi peralihan DC [Hz]	10000
Pelindung hubung singkat	ya
Pelindung beban berlebih	ya

Zona pendeteksian

Sensitivitas respons [mT]	2.8
Kecepatan pergerakan [m/s]	> 10

Akurasi/deviasi

Histeresis [mm]	< 1.5
-----------------	-------

MK500A



Sensor silinder T-slot

MKT3028BBPKG/G/ZH/3D

Kemampuan pengulangan	[mm]	< 0.2
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...60
Perlindungan		IP 65; IP 67
Pengujian/persetujuan		
Tanda ATEX		II 3D Ex tc IIIC T125°C Dc X
EME	EN 61000-4-2 ESD	- CD / 8 kV AD
	EN 61000-4-3 HF dipancarkan	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF dihantarkan	10 V
	EN 55011	kelas B
MTTF	[ANN]	3694
Data teknis		
Berat	[g]	59.4
Pemasangan		flush mountable
Tipe pemasangan		klem pengencang dengan slot kombinasi/soket segienam, lebar penampang 1,5
Tipe silinder		Silinder T-slot; (adaptor memungkinkan pemasangan pada tipe silinder yang berbeda)
Dimensi	[mm]	25 x 5 x 6.5
Material		PA; baja tahan karat
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		placeholder karet: 1
		Klip kabel: 1
		Tutup pelindung: 1 x T-Nut, E12259
Keterangan		
Jumlah paket		1 buah

MK500A




Sensor silinder T-slot

MKT3028BBPKG/G/ZH/3D

Koneksi listrik

Kabel: 2 m, PUR; 3 x 0.14 mm²

Koneksi



BK = Warna core :
BN = hitam
BU = coklat
 biru