


Sensor NAMUR induktif

IEA2001-N/6m PPU

Produk tidak tersedia - entri arsip

Produk alternatif: NE5012

Ketika memilih produk dan aksesoris alternatif, perhatikan bahwa data teknis mungkin berbeda!



Karakteristik produk

Fungsi output		biasanya tertutup
Jangkauan pendeteksian	[mm]	1
Casing		tipe berulir
Dimensi	[mm]	M8 x 1 / L = 30

Data kelistrikan

Tegangan nominal DC	[V]	8.2; (1kΩ)
Tegangan suplai DC	[V]	5...25
Konsumsi arus	[mA]	< 1; (dinonaktifkan; konduktif: > 2,1)

Output

Fungsi output		biasanya tertutup
Resistensi kabel maks.	[Ω]	50
Frekuensi peralihan DC	[Hz]	2000

Zona pendeteksian

Jangkauan pendeteksian	[mm]	1
------------------------	------	---

Kondisi pengoperasian

Suhu sekitar	[°C]	-20...70
Perlindungan		IP 67

Pengujian/persetujuan

Tahan guncangan/getaran		30 g (11 ms) / 10-55 Hz (1 mm)
-------------------------	--	--------------------------------

Klasifikasi keamanan

Kapasitansi internal maks.	[nF]	80
Induktansi internal maks.	[μH]	110

Data teknis

Casing		tipe berulir
Pemasangan		flush mountable
Dimensi	[mm]	M8 x 1 / L = 30
Penamaan ulir		M8 x 1

NE5007



Sensor NAMUR induktif

IEA2001-N/6m PPU

Material	kuningan berlapis nikel; PBT
----------	------------------------------

Aksesori

Item dikirim	mur pengunci: 2
--------------	-----------------


Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Kabel: 6 m, PUR / PVC; 2 x 0.14 mm²

Koneksi



BN =	Warna core :
BU =	coklat
	biru