


Sensor NAMUR induktif

IEA2001-N /PUR/KABEL/SVART

Produk tidak tersedia - entri arsip



Karakteristik produk

Fungsi output		biasanya tertutup
Jangkauan pendeteksian	[mm]	1
Casing		tipe berulir
Dimensi	[mm]	M8 x 1 / L = 30

Data kelistrikan

Tegangan nominal DC	[V]	8.2; (1k Ω)
Tegangan suplai DC	[V]	5...25
Konsumsi arus	[mA]	< 1; (dinonaktifkan; konduktif: > 2,1)

Output

Fungsi output		biasanya tertutup
Resistensi kabel maks.	[Ω]	50
Frekuensi peralihan DC	[Hz]	2000

Zona pendeteksian

Jangkauan pendeteksian	[mm]	1
------------------------	------	---

Kondisi pengoperasian

Suhu sekitar	[°C]	-20...70
Perlindungan		IP 67

Pengujian/persetujuan

Tahan guncangan/getaran		30 g (11 ms) / 10-55 Hz (1 mm)
-------------------------	--	--------------------------------

Klasifikasi keamanan

Kapasitansi internal maks.	[nF]	80
Induktansi internal maks.	[μ H]	110

Data teknis

Casing		tipe berulir
Pemasangan		flush mountable
Dimensi	[mm]	M8 x 1 / L = 30
Penamaan ulir		M8 x 1
Material		kuningan berlapis nikel; PBT

Aksesori

Item dikirim		mur pengunci: 2
--------------	--	-----------------

NE5009



Sensor NAMUR induktif

IEA2001-N /PUR/KABEL/SVART

Keterangan


Jumlah paket

1 buah

Koneksi listrik

Kabel: 2 m, PUR; 2 x 0.14 mm²

Koneksi



BN =

Warna core :
coklat

BU =

biru