


MK5305



Sensor silinder C-slot

MKC3028-BPKG/G/0,5M/ZH/ASR



- 1 klem pengencang
2 Permukaan pendeteksian



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Dimensi [mm]	17.5 x 2.8 x 7.7

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC; ("kelas suplai 2" menurut cULus)
Konsumsi arus [mA]	< 10
Kelas perlindungan	III
Pelindung polaritas terbalik	ya
Waktu penundaan pengaktifan maks. [ms]	30

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	100
Frekuensi peralihan DC [Hz]	10000
Pelindung hubung singkat	ya
Pelindung beban berlebih	ya

Zona pendeteksian

Sensitivitas respons [mT]	2.8
Kecepatan pergerakan [m/s]	> 10

Akurasi/deviasi

Histeresis [mm]	1.5
Kemampuan pengulangan [mm]	< 0.2

MK5305



Sensor silinder C-slot

MKC3028-BPKG/G/0,5M/ZH/ASR

Kondisi pengoperasian

Suhu sekitar	[°C]	-25...85
Perlindungan		IP 65; IP 67

Pengujian/persetujuan

EME	EN 61000-4-2 ESD	- CD / 8 kV AD
	EN 61000-4-3 HF dipancarkan	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF dihantarkan	10 V
	EN 55011	kelas B
MTTF	[ANN]	3694
Persetujuan UL	Persetujuan UL no.	C008

Data teknis

Berat	[g]	13.5
Pemasangan		non-flush mountable
Tipe silinder		Silinder C-slot
Dimensi	[mm]	17.5 x 2.8 x 7.7
Material		casing: PA; klem pengencang: baja tahan karat

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
---------	------------------	-----------------

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik - colokan

Kabel: 0.5 m, PUR

Konektor: 1 x M8; pengkodean: A; Penguncian: mur bergerigi, dapat diputar



Koneksi

