


MK5352



Sensor silinder C-slot

MKC3028-BPKG/G/0,3M/ZH/AS



- 1 klem pengencang
- 2 Permukaan pendeteksian



Karakteristik produk		
Desain kelistrikan		PNP
Fungsi output		biasanya terbuka
Dimensi	[mm]	17.5 x 2.8 x 7.7
Data kelistrikan		
Tegangan pengoperasian	[V]	10...30 DC; ("kelas suplai 2" menurut cULus)
Konsumsi arus	[mA]	< 10
Kelas perlindungan		III
Pelindung polaritas terbalik		ya
Waktu penundaan pengaktifan maks.	[ms]	30
Output		
Desain kelistrikan		PNP
Fungsi output		biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC	[V]	2.5
Peringkat arus permanen dari output peralihan DC	[mA]	100
Frekuensi peralihan DC	[Hz]	10000
Pelindung hubung singkat		ya
Tipe pelindung hubung singkat		berpulsa
Pelindung beban berlebih		ya
Zona pendeteksian		
Sensitivitas respons	[mT]	2.8
Kecepatan pergerakan	[m/s]	> 10
Akurasi/deviasi		
Histeresis	[mm]	1.5

MK5352



Sensor silinder C-slot

MKC3028-BPKG/G/0,3M/ZH/AS

Kemampuan pengulangan	[mm]	< 0.2
-----------------------	------	-------

Kondisi pengoperasian

Suhu sekitar	[°C]	-25...85
Perlindungan		IP 65; IP 67

Pengujian/persetujuan

EME	EN 61000-4-2 ESD	- CD / 8 kV AD
	EN 61000-4-3 HF dipancarkan	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF dihantarkan	10 V
	EN 55011	kelas B
Persetujuan UL	Persetujuan UL no.	C008

Data teknis

Berat	[g]	12.4
Pemasangan		non-flush mountable
Tipe silinder		Silinder C-slot
Dimensi	[mm]	17.5 x 2.8 x 7.7
Material		casing: PA; klem pengencang: baja tahan karat; tabung pelindung: PTFE

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
---------	------------------	-----------------


Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik - colokan

Kabel: 0.3 m, PUR; tabung pelindung

Konektor: 1 x M8; pengkodean: A; Penguncian: snap-fit



Koneksi

