




Sensor silinder dengan sel GMR

MKC2028BARKG/G/0.3M/ZH/AS



1 klem pengencang



Karakteristik produk

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Dimensi [mm]	26.1 x 2.8 x 5.5

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	< 10
Kelas perlindungan	III
Pelindung polaritas terbalik	ya
Waktu penundaan pengaktifan maks. [ms]	30

Output

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	4.5
Arus beban minimal [mA]	5
Kebocoran arus maks. [mA]	0.8
Peringkat arus permanen dari output peralihan DC [mA]	100
Frekuensi peralihan DC [Hz]	4000
Pelindung hubung singkat	ya
Pelindung beban berlebih	ya

Zona pendeteksian

Sensitivitas respons [mT]	2.8
Kecepatan pergerakan [m/s]	> 10

Akurasi/deviasi

Histeresis [mm]	< 0.12
-----------------	--------



Sensor silinder dengan sel GMR

MKC2028BARKG/G/0.3M/ZH/AS

Kemampuan pengulangan [mm] < 0.2

Kondisi pengoperasian

Suhu sekitar [°C] -25...85

Perlindungan IP 65; IP 67

Pengujian/persetujuan

EME	EN 61000-4-2 ESD	- CD / 8 kV AD
	EN 61000-4-3 HF dipancarkan	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF dihantarkan	10 V
	EN 55011	kelas B
Ketahanan terhadap getaran	EN 60947-5-2	
Tahan guncangan	EN 60947-5-2	

Data teknis

Berat [g]	9.8
Pemasangan	flush mountable
Tipe silinder	Silinder C-slot
Dimensi [mm]	26.1 x 2.8 x 5.5
Material	casing: PA; klem pengencang: baja tahan karat

Elemen display/pengoperasian

Display status peralihan 1 x LED, kuning

Keterangan

Jumlah paket 1 buah

Koneksi listrik - colokan

Kabel: 0.3 m, PUR

Konektor: 1 x M8; pengkodean: A; Penguncian: snap-fit



Koneksi

