


Sensor NAMUR induktif

IFA2004-N/PH/AMP

Produk tidak tersedia - entri arsip



Karakteristik produk

Fungsi output		biasanya tertutup
Jangkauan pendeteksian	[mm]	4
Casing		tipe berulir
Dimensi	[mm]	M12 x 1

Data kelistrikan

Tegangan nominal DC	[V]	8.2; (1k Ω)
Tegangan suplai DC	[V]	5...25
Konsumsi arus	[mA]	< 1; (dinonaktifkan; konduktif: > 2,1)

Output

Fungsi output		biasanya tertutup
Resistensi kabel maks.	[Ω]	50
Frekuensi peralihan DC	[Hz]	400

Zona pendeteksian

Jangkauan pendeteksian	[mm]	4
------------------------	------	---

Kondisi pengoperasian

Suhu sekitar	[°C]	-20...70
Perlindungan		IP 67

Pengujian/persetujuan

Tahan guncangan/getaran		30 g (11 ms) / 10-55 Hz (1 mm)
-------------------------	--	--------------------------------

Klasifikasi keamanan

Kapasitansi internal maks.	[nF]	230
----------------------------	------	-----



Sensor NAMUR induktif

IFA2004-N/PH/AMP

Induktansi internal maks.	[μH]	170
---------------------------	------	-----

Data teknis

Casing	tipe berulir
Pemasangan	non-flush mountable
Dimensi	[mm] M12 x 1
Penamaan ulir	M12 x 1
Material	kuningan berlapis nikel; PBT

Aksesori

Item dikirim	mur pengunci: 2
--------------	-----------------


Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Kabel: 2 m, PUR; 2 x 0.34 mm²

Koneksi



BK = Warna core :
 WH = hitam
 putih

Konektor: 1 x AMP