

NE5010




Sensor NAMUR induktif

IEA2001-N/Sonderkonfektion

Produk tidak tersedia - entri arsip

Produk alternatif: NE5001
Ketika memilih produk dan aksesoris alternatif, perhatikan bahwa data teknis mungkin berbeda!




Karakteristik produk		
Fungsi output		biasanya tertutup
Jangkauan pendeteksian	[mm]	1
Casing		tipe berulir
Dimensi	[mm]	M8 x 1
Data kelistrikan		
Tegangan nominal DC	[V]	8.2; (1kΩ)
Tegangan suplai DC	[V]	5...25
Konsumsi arus	[mA]	< 1; (dinonaktifkan; konduktif: > 2,1)
Output		
Fungsi output		biasanya tertutup
Resistensi kabel maks.	[Ω]	50
Frekuensi peralihan DC	[Hz]	2000
Zona pendeteksian		
Jangkauan pendeteksian	[mm]	1
Kondisi pengoperasian		
Suhu sekitar	[°C]	-20...70
Perlindungan		IP 67



Sensor NAMUR induktif

IEA2001-N/Sonderkonfektion

Pengujian/persetujuan	
Tahan guncangan/getaran	30 g (11 ms) / 10-55 Hz (1 mm)
Klasifikasi keamanan	
Kapasitansi internal maks. [nF]	80
Induktansi internal maks. [μH]	110
Data teknis	
Casing	tipe berulir
Pemasangan	flush mountable
Dimensi [mm]	M8 x 1
Penamaan ulir	M8 x 1
Material	kuningan berlapis nikel; PBT
Aksesori	
Item dikirim	mur pengunci: 2
Keterangan	
Jumlah paket	1 buah
Koneksi listrik	
Kabel: 2 m, PVC; 2 x 0.14 mm ²	
Koneksi	



BN = Warna core :
 BU = coklat
 biru

Konektor: 1 x M25