


NT5001



Induktiver NAMUR-Sensor

ITA2001-N/1D/1G



Karakteristik produk

Desain kelistrikan	NAMUR
Fungsi output	biasanya tertutup
Jangkauan pendeteksian [mm]	1
Casing	berbentuk silinder
Dimensi [mm]	Ø 6.5 / L = 30

Data kelistrikan

Koneksi ke amplifier pengalih	ya
Amplifier pengalih	koneksi ke sirkuit tersertifikasi yang aman secara intrinsik dengan nilai maks.: U = 15 V / I = 50 mA / P = 120 mW
Tegangan nominal DC [V]	8.2; (1kΩ)
Tegangan suplai DC [V]	7.5...30; (jika digunakan di luar area berbahaya)
Konsumsi arus [mA]	< 1; (dinonaktifkan; konduktif: > 2,1)
Kelas perlindungan	III

Output

Desain kelistrikan	NAMUR
Fungsi output	biasanya tertutup
Peringkat arus permanen dari output peralihan DC [mA]	30; (jika digunakan di luar area berbahaya)
Frekuensi peralihan DC [Hz]	2000

Zona pendeteksian

Jangkauan pendeteksian [mm]	1
Jangkauan pendeteksian real Sr [mm]	1 ± 10 %

Akurasi/deviasi

Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.5 / aluminium: 0.4 / tembaga: 0.3
Histeresis [X01]	1...15
Deviasi titik peralihan [X01]	-10...10

Kondisi pengoperasian

Suhu sekitar [°C]	-20...80
Perlindungan	IP 67

Pengujian/persetujuan

Persetujuan	PTB 01 ATEX 2191; BVS 04 ATEX E 153 X; IECEx BVS 06.0003X
Tanda ATEX	Ex II 1G Ex ia IIC T6 Ga Ta -20...70°C
	Ex II 1G Ex ia IIC T5 Ga Ta -20...80°C

NT5001



Induktiver NAMUR-Sensor

ITA2001-N/1D/1G

		 II 1D Ex ia IIIC T20090°C Da Ta: -20...70°C
		 II 1D Ex ia IIIC T200100° C Da Ta: -20...80°C
EME	EN 60947-5-6	
Tahan guncangan/getaran	30 g (11 ms) / 10-55 Hz (1 mm)	
MTTF	[ANN]	4816

Klasifikasi keamanan

Kapasitansi internal maks.	[nF]	80
Induktansi internal maks.	[μH]	70

Data teknis

Berat	[g]	116
Casing	berbentuk silinder	
Pemasangan	flush mountable	
Dimensi	[mm]	Ø 6.5 / L = 30
Material	kuningan lapisan khusus; permukaan pendeteksian: PBT	


Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Kabel: 2 m, PVC; 2 x 0.14 mm²

Koneksi



BN =	Warna core :
BU =	coklat
	biru