


O2M211



Kamera analog untuk mesin bergerak

O2MXOOKG/A1/GM/170/M



Karakteristik produk

Resolusi gambar	[px]	640 x 480
Sudut bukaan	[°]	170 x 117

Aplikasi

Fitur khusus	Kabel berpelindung
Aplikasi	Fungsi pemantulan terintegrasi

Data kelistrikan

Tegangan pengoperasian	[V]	12...32 DC
Konsumsi arus	[mA]	< 280; (dengan pemanas lensa)
Pelindung tegangan berlebih		ya
Sensor gambar		sensor gambar 1/4" 4:3 VGA CMOS Color
Arus puncak pengaktifan	[mA]	1000



Kamera analog untuk mesin bergerak

O2MXOOKG/A1/GM/170/M

Durasi arus puncak pengaktifan	[ms]	2
--------------------------------	------	---

Output

Output video	PAL (25 fps interlace) 720H x 576V (640 x 480), 1 Vtt / 75 Ω
--------------	--

Zona pendeteksian

Ukuran bidang pandang	[mm]	Jarak pengoperasian [m]	bidang pandang [m]		
		1	22,86 x 3,26		
		2	45,72 x 6,53		
		3	68,58 x 9,79		
		4	91,44 x 13,05		
		5	114,30 x 16,32		
Resolusi gambar	[px]	640 x 480			
Sudut bukaan	[°]	170 x 117			
Sensitivitas cahaya	[LUX]	< 0.05			
Rentang dinamis	[dB]	> 80			

Kondisi pengoperasian

Suhu sekitar	[°C]	-40...85
Suhu penyimpanan	[°C]	-40...100
Perlindungan		IP 67; IP 69K

Pengujian/persetujuan

EME	DIN EN 61000-6-4	lingkungan industri
	DIN EN 61000-6-2	lingkungan industri
	UN-ECE R10	
Tahan guncangan		50 g
Ketahanan terhadap getaran	Jangkauan frekuensi 24...2000 Hz	(15.3 x 9.81 m/s²)rms
	PSD (g²/Hz)	0.04...0.1
Pengujian semprotan garam	IEC 60068-5-52	

Data teknis

Berat	[g]	301.7
Dimensi	[mm]	Ø 55 / L = 52
Material		casing: PC/ABS; lensa depan: poliamida diperkuat dengan serat kaca

Aksesori

Item dikirim	Set pemasangan: E2M210
	sekrup: 2 x M6 x 20
	washer
	Mur: 2 x M6, penguncian otomatis
	lapisan anti-selip

Keterangan

Jumlah paket	1 buah
--------------	--------



Kamera analog untuk mesin bergerak

O2MXOOKG/A1/GM/170/M

Koneksi listrik

Kabel: 0.5 m, berpelindung; pelindung terhubung

Konektor: 1 x M16; pengkodean: A; Kabel koneksi berpelindung: true



1	core kabel coax sinyal video
2	layar coax GND video
3	U+
4	0 V