


O2M200



Kamera analog untuk mesin bergerak

O2MXOOKG/A1/GM/78



Karakteristik produk

Resolusi gambar	[px]	640 x 480
Sudut bukaan	[°]	80 x 59

Aplikasi

Fitur khusus	Kabel berpelingung
--------------	--------------------

Data kelistrikan

Tegangan pengoperasian	[V]	12...32 DC
Konsumsi arus	[mA]	< 280; (dengan pemanas lensa)
Pelindung tegangan berlebih		ya
Sensor gambar		sensor gambar 1/4" 4:3 VGA CMOS Color

O2M200



Kamera analog untuk mesin bergerak

O2MXOOKG/A1/GM/78

Arus puncak pengaktifan	[mA]	1000			
Durasi arus puncak pengaktifan	[ms]	2			
Output					
Output video		PAL (25 fps interlace) 720H x 576V (640 x 480), 1 Vtt / 75 Ω			
Zona pendeteksian					
Ukuran bidang pandang	[mm]	Jarak pengoperasian	bidang pandang		
		1000	1680 x 1130		
		2000	3360 x 2260		
		3000	5030 x 3390		
		4000	6710 x 4530		
		5000	8390 x 5660		
Resolusi gambar	[px]	640 x 480			
Sudut bukaan	[°]	80 x 59			
Sensitivitas cahaya	[LUX]	< 0.05			
Rentang dinamis	[dB]	> 80			
Kondisi pengoperasian					
Suhu sekitar	[°C]	-40...85			
Suhu penyimpanan	[°C]	-40...100			
Perlindungan		IP 67; IP 69K			
Pengujian/persetujuan					
EME		DIN EN 61000-6-4	lingkungan industri		
		DIN EN 61000-6-2	lingkungan industri		
		UN-ECE R10			
Tahan guncangan			50 g		
Ketahanan terhadap getaran		Jangkauan frekuensi 24...2000 Hz	(15.3 x 9.81 m/s²)rms		
		PSD (g²/Hz)	0.04...0.1		
Pengujian semprotan garam		IEC 60068-5-52			
Data teknis					
Berat	[g]	311			
Dimensi	[mm]	Ø 55.5 / L = 51.3			
Material		casing: PC/ABS; lensa depan: poliamida diperkuat dengan serat kaca			
Aksesori					
Item dikirim		Set pemasangan:, E2M210			
		sekrup: 2 x M6 x 20			
		washer			
		Mur: 2 x M6, penguncian otomatis			
		lapisan anti-selip			
Keterangan					
Jumlah paket		1 buah			



Kamera analog untuk mesin bergerak

O2MXOOKG/A1/GM/78

Koneksi listrik

Kabel: 0.5 m, berpelindung

Konektor: 1 x M16; pengkodean: A; Kabel koneksi berpelindung: pelindung terhubung



1	core kabel coax sinyal video
2	layar coax GND video
3	U+
4	0 V