


O7E200



Receiver sensor sinar tembus

O7E-DPKG/0,20M/AS



receiver di lensa atas



Karakteristik produk

Tipe cahaya	cahaya merah
Casing	persegi panjang

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	10; ((24 V))
Kelas perlindungan	III
Pelindung polaritas terbalik	ya
Tipe cahaya	cahaya merah

Output

Desain kelistrikan	PNP
Fungsi output	mode dark-on
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	100
Frekuensi peralihan DC [Hz]	1000
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa

Zona pendeteksian

Transmitter/receiver	receiver
Jarak jangkauan [m]	0...1.5
Jangkauan yang dapat disesuaikan	tidak
Dimensi titik cahaya mengacu pada	pada jangkauan maksimum



Receiver sensor sinar tembus

O7E-DPKG/0,20M/AS

Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...60
Perlindungan		IP 65
Pengujian/persetujuan		
EME	EN 60947-5-2	
MTTF	[ANN]	1312
Data teknis		
Berat	[g]	14.5
Casing		persegi panjang
Dimensi	[mm]	20.3 x 15 x 9
Material		PA
Material lensa		PMMA
Penyelarasan lensa		lensa samping
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Keterangan		
Keterangan	tegangan pengoperasian "kelas suplai 2" menurut UL	
Jumlah paket	1 buah	
Koneksi listrik		
Kabel: 0.2 m, PUR; 3 x 0.14 mm²		
Konektor: 1 x M8; pengkodean: A; Penguncian: snap-fit		
		
Koneksi		