


O7S200



Transmitter sensor sinar tembus

O7S-OOKG/0,20M/AS



transmitter di lensa atas



Karakteristik produk

Tipe cahaya	cahaya merah
Casing	persegi panjang

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	20; ((24 V))
Kelas perlindungan	III
Pelindung polaritas terbalik	ya
Tipe cahaya	cahaya merah
Panjang gelombang [nm]	633

Output

Frekuensi peralihan DC [Hz]	1000
-----------------------------	------

Zona pendeteksian

Transmitter/receiver	transmitter
Jarak jangkauan [m]	0...1.5
Jangkauan yang dapat disesuaikan	tidak
Diameter titik cahaya maks. [mm]	90
Dimensi titik cahaya mengacu pada	pada jangkauan maksimum

Kondisi pengoperasian

Suhu sekitar [°C]	-25...60
Perlindungan	IP 65

Pengujian/persetujuan

EME	EN 60947-5-2
MTTF [ANN]	1899



Transmitter sensor sinar tembus

O7S-OOKG/0,20M/AS

Data teknis

Berat	[g]	14.2
Casing		persegi panjang
Dimensi	[mm]	20.3 x 15 x 9
Material		PA
Material lensa		PMMA
Penyelarasan lensa		lensa samping

Elemen display/pengoperasian

Display	operasi	1 x LED, hijau
---------	---------	----------------


Keterangan

Keterangan	tegangan pengoperasian "kelas suplai 2" menurut UL
Jumlah paket	1 buah

Koneksi listrik

Kabel: 0.2 m, PUR; 3 x 0.14 mm²

Konektor: 1 x M8; pengkodean: A; Penguncian: snap-fit



Koneksi

