


O5E700



Receiver sensor laser sinar tembus

O5ELFPKG/US100



Karakteristik produk		
Tipe cahaya		cahaya merah
Casing		persegi panjang
Aplikasi		
Prinsip fungsi		Sensor sinar tembus
Data kelistrikan		
Tegangan pengoperasian	[V]	10...36 DC
Konsumsi arus	[mA]	11
Kelas perlindungan		II
Pelindung polaritas terbalik		ya
Tipe cahaya		cahaya merah
Panjang gelombang	[nm]	655
Output		
Desain kelistrikan		PNP
Fungsi output		mode light-on/dark-on; (dapat diprogram)
Penurunan tegangan maks. pada output peralihan DC	[V]	2.5



Receiver sensor laser sinar tembus

O5ELFPKG/US100

Peringkat arus permanen dari output peralihan DC [mA]	200
Frekuensi peralihan DC [Hz]	1000
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian

Transmitter/receiver	receiver
Jarak jangkauan [m]	< 60
Jangkauan yang dapat disesuaikan	ya
Diameter objek terkecil yang dapat dideteksi [mm]	3; (60 m)

Kondisi pengoperasian

Suhu sekitar [°C]	-10...60
Perlindungan	IP 67

Pengujian/persetujuan

EME	EN 60947-5-2
MTTF [ANN]	788

Data teknis

Berat [g]	67.5
Casing	persegi panjang
Dimensi [mm]	56 x 18.2 x 46.8
Material	casing: PA; bezel: baja tahan karat; interface operator: TPU
Material lensa	PMMA
Penyelarasan lensa	lensa samping

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
Fungsi adaptasi		ya
Kunci elektronik		ya

Keterangan

Keterangan	tegangan pengoperasian "kelas suplai 2" menurut cULus
Jumlah paket	1 buah

Koneksi listrik

Konektor: 1 x M12; pengkodean: A



O5E700



Receiver sensor laser sinar tembus

O5ELFPKG/US100

Koneksi

