


O6S215



Transmitter sensor sinar tembus

O6SIOOKG/AS/4P



1: emisi cahaya



Karakteristik produk

Tipe cahaya	cahaya inframerah
Casing	persegi panjang

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	11; ((24 V))
Kelas perlindungan	III
Tipe cahaya	cahaya inframerah
Panjang gelombang [nm]	850

Zona pendeteksian

Transmitter/receiver	transmitter
Jarak jangkauan [m]	< 15
Diameter titik cahaya maks. [mm]	460
Dimensi titik cahaya mengacu pada	pada jangkauan maksimum

Kondisi pengoperasian

Suhu sekitar [°C]	-25...60
Perlindungan	IP 65; IP 67

Pengujian/persetujuan

EME	EN 60947-5-2	
MTTF [ANN]	2920	
Persetujuan UL	Persetujuan UL no.	E002



Transmitter sensor sinar tembus

O6SIOOKG/AS/4P

Data teknis		
Berat	[g]	17.7
Casing		persegi panjang
Dimensi	[mm]	35.4 x 13 x 21
Material		casing: ABS; PPSU
Material lensa		PMMA
Penyelarasan lensa		lensa samping
Material penyegel		EPDM
Torsi pengencangan	[Nm]	0.5


Elemen display/pengoperasian		
Display	operasi	1 x LED, hijau
Keterangan		
Keterangan		tegangan pengoperasian "kelas suplai 2" menurut cULus
Jumlah paket		1 buah

Koneksi listrik

Konektor: 1 x M8; pengkodean: A; Penguncian: logam, dilapisi; Segel: EPDM



Koneksi



Transmitter sensor sinar tembus

O6SIOOKG/AS/4P

Diagram dan grafik

grafik excess gain

