


O6S301



Transmitter sensor sinar tembus

O6S-OOKG/0,30m/US




Karakteristik produk		
Tipe cahaya		cahaya merah
Casing		persegi panjang
Aplikasi		
Prinsip fungsi		Sensor sinar tembus
Data kelistrikan		
Tegangan pengoperasian	[V]	10...30 DC
Konsumsi arus	[mA]	11; ((24 V))
Kelas perlindungan		III
Tipe cahaya		cahaya merah
Panjang gelombang	[nm]	633
Zona pendeteksian		
Transmitter/receiver		transmitter
Jarak jangkauan	[m]	< 10
Diameter titik cahaya maks.	[mm]	300
Dimensi titik cahaya mengacu pada		pada jangkauan maksimum
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 65; IP 67; IP 68; IP 69K
Pengujian/persetujuan		
EME	EN 60947-5-2	
MTTF	[ANN]	2600
Persetujuan UL	Persetujuan UL no.	E005



Transmitter sensor sinar tembus

O6S-OOKG/0,30m/US


Data teknis		
Berat	[g]	50.5
Casing		persegi panjang
Material		casing: baja tahan karat (1.4404 / 316L); plastik: PPSU; Segel: EPDM
Material lensa		PMMA
Penyelarasan lensa		lensa samping
Torsi pengencangan	[Nm]	1; (sekrup)
Elemen display/pengoperasian		
Display	operasi	1 x LED, hijau
Keterangan		
Keterangan		tegangan pengoperasian "kelas suplai 2" menurut cULus
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 0.3 m, PVC; 2 x 0.25 mm ²		
Konektor: 1 x M12; pengkodean: A		
		
Koneksi		
		

Transmitter sensor sinar tembus

O6S-OOKG/0,30m/US

Diagram dan grafik

grafik excess gain



x: jarak [mm]

y: faktor excess gain