

O8E205



Receiver sensor sinar tembus

O8E-DNKG/0,30M/AS/4P



1 receiver di lensa atas
ilustrasi (contoh)



Karakteristik produk

Tipe cahaya	cahaya merah
Casing	persegi panjang

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Data kelistrikan

Tegangan pengoperasian	[V]	10...30 DC
Konsumsi arus	[mA]	15; ((24 V))
Kelas perlindungan		III
Pelindung polaritas terbalik		ya
Tipe cahaya		cahaya merah
Panjang gelombang	[nm]	633

Output

Desain kelistrikan		NPN
Fungsi output		mode dark-on
Penurunan tegangan maks. pada output peralihan DC	[V]	2.5



Receiver sensor sinar tembus

O8E-DNKG/0,30M/AS/4P

Peringkat arus permanen dari output peralihan DC [mA]	100
Frekuensi peralihan DC [Hz]	1000
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa

Zona pendeteksian

Transmitter/receiver	receiver
Jarak jangkauan [m]	< 3

Kondisi pengoperasian

Suhu sekitar [°C]	-25...60
Perlindungan	IP 65; IP 67

Pengujian/persetujuan

EME	EN 60947-5-2	
MTTF [ANN]	1152	
Persetujuan UL	Ta	-25...60 °C
	Tipe penutup	Type 1
	suplai tegangan	Limited Voltage/Current
	Persetujuan UL no.	E015
	Nomor file UL	E174191

Data teknis

Berat [g]	23.1
Casing	persegi panjang
Dimensi [mm]	28.1 x 8.1 x 14.4
Material	casing: ABS; baja tahan karat (1.4404 / 316L)
Material lensa	PMMA
Penyelarasan lensa	lensa samping

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
	operasi	1 x LED, hijau

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Kabel: 0.3 m, PVC, hitam, Ø 2.9 mm; 3 x 0.08 mm²

Konektor: 1 x M8; pengkodean: A



Receiver sensor sinar tembus

O8E-DNKG/0,30M/AS/4P

Koneksi




Diagram dan grafik

grafik excess gain



x: jarak [mm]

y: faktor excess gain