


Receiver sensor laser sinar tembus

OGELFPKG/US100



1 tombol pemrograman



Karakteristik produk

Tipe cahaya	cahaya merah
Casing	tipe berulir

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	11
Kelas perlindungan	II
Pelindung polaritas terbalik	ya
Tipe cahaya	cahaya merah
Panjang gelombang [nm]	655
Tipe masa pakai [h]	50000

Output

Desain kelistrikan	PNP
Fungsi output	mode light-on/dark-on; (dapat diprogram)
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	200
Frekuensi peralihan DC [Hz]	1000
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian

Transmitter/receiver	receiver
Jarak jangkauan [m]	< 60
Pengaturan pabrik	mode dark-on



Receiver sensor laser sinar tembus

OGELFPKG/US100

Jangkauan yang dapat disesuaikan	ya	
Diameter objek terkecil yang dapat dideteksi [mm]	3; (60 m)	
Kondisi pengoperasian		
Suhu sekitar [°C]	-10...60	
Perlindungan	IP 65; IP 67	
Pengujian/persetujuan		
EME	EN 60947-5-2	
MTTF [ANN]	786	
Data teknis		
Berat [g]	61.9	
Casing	tipe berulir	
Dimensi [mm]	M18 x 1 / L = 72	
Penamaan ulir	M18 x 1	
Material	baja tahan karat (1.4404 / 316L); PA; LCP; EPDM; TPU	
Material lensa	PMMA	
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim	mur pengunci: 2	
Keterangan		
Keterangan	tegangan pengoperasian "kelas suplai 2" menurut cULus	
Jumlah paket	1 buah	
Koneksi listrik		
Konektor: 1 x M12; pengkodean: A		
		



Receiver sensor laser sinar tembus

OGELFPKG/US100

Koneksi

