

Receiver sensor sinar tembus

OGE-DBOW/LS/CUBE

Produk tidak tersedia - entri arsip



Karakteristik produk

Tipe cahaya	cahaya merah
Casing	rectangular with M18 thread

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Data kelistrikan

Frekuensi AC	[Hz]	47...63
Tegangan pengoperasian	[V]	20...250 AC
Kelas perlindungan		II; (double insulated)
Tipe cahaya		cahaya merah
Panjang gelombang	[nm]	633

Output

Fungsi output		mode dark-on
Penurunan tegangan maks. pada output peralihan AC	[V]	8
Arus beban minimal	[mA]	5
Kebocoran arus maks.	[mA]	1.7
Peringkat arus permanen dari output peralihan AC	[mA]	150; (200 (...40 °C))
Peringkat arus jangka pendek dari output peralihan	[mA]	1200; (20 ms / 0,5 Hz)
Frekuensi peralihan AC	[Hz]	30
Pelindung hubung singkat		tidak
Pelindung beban berlebih		tidak

Zona pendeteksian

Transmitter/receiver		receiver
Jarak jangkauan	[m]	< 20



Receiver sensor sinar tembus

OGE-DBOW/LS/CUBE

Jangkauan yang dapat disesuaikan	tidak
----------------------------------	-------

Kondisi pengoperasian

Suhu sekitar [°C]	-25...60
Perlindungan	IP 67

Pengujian/persetujuan

EME	EN 60947-5-2	
	EN 55011 emisi	kelas B

Data teknis

Berat [g]	61
Casing	rectangular with M18 thread
Dimensi [mm]	52.6 x 19.1 x 36.9
Penamaan ulir	M18 x 1
Material	seng tuang; PEI
Material lensa	PMMA
Penyelarasan lensa	lensa samping

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
---------	------------------	-----------------

Koneksi listrik

Perlindungan yang diperlukan	sekring miniatur sesuai IEC60127-2 lembar 1; ≤ 2 A; cepat
------------------------------	--

Aksesori

Item dikirim	mur pengunci: 1
--------------	-----------------

Keterangan

Keterangan	Jangan menghubungkan tanpa beban.
Jumlah paket	1 buah

Koneksi listrik

Konektor: 1 x 1/2"; pengkodean: C



Receiver sensor sinar tembus

OGE-DBOW/LS/CUBE


Koneksi



Catatan : sekring miniatur sesuai IEC60127-2 lembar 1 ≤ 2 A cepat

Diagram dan grafik

grafik excess gain



x: Abstand [m]

y: Funktionsreservefaktor