


Receiver sensor sinar tembus

OGE-DPKG/US/V4A/CUBE IR

spesifik pelanggan



Karakteristik produk

Tipe cahaya	cahaya inframerah
Casing	persegi panjang

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	16
Kelas perlindungan	III
Pelindung polaritas terbalik	ya
Tipe cahaya	cahaya inframerah
Panjang gelombang [nm]	860

Output

Desain kelistrikan	PNP
Fungsi output	mode dark-on
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	200
Frekuensi peralihan DC [Hz]	1000
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian

Transmitter/receiver	receiver
Jarak jangkauan [m]	< 15



Receiver sensor sinar tembus

OGE-DPKG/US/V4A/CUBE IR

Jangkauan yang dapat disesuaikan	tidak
----------------------------------	-------

Kondisi pengoperasian

Suhu sekitar [°C]	-25...80
Suhu penyimpanan [°C]	-40...80
Perlindungan	IP 65; IP 67; IP 68; IP 69K

Pengujian/persetujuan

EME	EN 60947-5-2
MTTF [ANN]	961

Data teknis

Berat [g]	78
Casing	persegi panjang
Dimensi [mm]	52.9 x 20 x 34.6
Penamaan ulir	M18 x 1
Material	1.4542 (17-4 PH / 630); PEI
Material lensa	PEI
Penyelarasan lensa	lensa samping

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
	operasi	1 x LED, hijau

Aksesori

Item dikirim	mur pengunci: 1, baja tahan karat
--------------	-----------------------------------

Keterangan

Keterangan	
Catatan	spesifik pelanggan
Jumlah paket	1 buah

Koneksi listrik

Konektor: 1 x M12; pengkodean: A





Receiver sensor sinar tembus

OGE-DPKG/US/V4A/CUBE IR

Koneksi

