

Sensor refleksi difus

OGT-FPKG/6M



- 1 tombol pemrograman
2 LED 4 x 90°



Karakteristik produk

Tipe cahaya	cahaya merah
Casing	tipe berulir

Aplikasi

Prinsip fungsi	Sensor refleksi difus
----------------	-----------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	25
Kelas perlindungan	II
Pelindung polaritas terbalik	ya
Tipe cahaya	cahaya merah

Output

Desain kelistrikan	PNP
Fungsi output	mode light-on/dark-on; (dapat diprogram)
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	150; (200 (...60 °C))
Frekuensi peralihan DC [Hz]	2000
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian

Jarak jangkauan [mm]	2...800; (kertas putih 200 x 200 mm remisi 90%)
Pengaturan pabrik	mode light-on
Rentang pengaturan [mm]	150...800
Jangkauan yang dapat disesuaikan	ya
Diameter titik cahaya maks. [mm]	66



Sensor refleksi difus

OGT-FPKG/6M

Dimensi titik cahaya mengacu pada	pada jangkauan maksimum
-----------------------------------	-------------------------

Kondisi pengoperasian

Suhu sekitar [°C]	-25...80
Perlindungan	IP 65; IP 67; IP 68; IP 69K

Pengujian/persetujuan

EME	EN 60947-5-2
MTTF [ANN]	473

Data teknis

Berat [g]	255
Casing	tipe berulir
Dimensi [mm]	M18 x 1 / L = 80.4
Penamaan ulir	M18 x 1
Material	baja tahan karat (1.4404 / 316L); PA; LCP; EPDM; TPU
Material lensa	PMMA

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
Fungsi adaptasi		ya
Kunci elektronik		ya

Aksesori

Item dikirim	mur pengunci: 2
--------------	-----------------


Keterangan

Keterangan	tegangan pengoperasian "kelas suplai 2" menurut cULus
Jumlah paket	1 buah

Koneksi listrik

Kabel: 6 m, PVC; 3 x 0.34 mm²

Koneksi



	Warna core :
BK =	hitam
BN =	coklat
BU =	biru



Sensor refleksi difus

OGT-FPKG/6M

Diagram dan grafik

grafik excess gain

