


Transmitter sensor sinar tembus

OGS-OOKG/2M



1 x LED 4 x 90°



Karakteristik produk

Tipe cahaya	cahaya merah
Casing	tipe berulir

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	20
Kelas perlindungan	II
Pelindung polaritas terbalik	ya
Tipe cahaya	cahaya merah
Panjang gelombang [nm]	624

Zona pendeteksian

Transmitter/receiver	transmitter
Jarak jangkauan [m]	< 25
Diameter titik cahaya maks. [mm]	1000
Dimensi titik cahaya mengacu pada	pada jangkauan maksimum

Kondisi pengoperasian

Suhu sekitar [°C]	-25...80
Perlindungan	IP 67

Pengujian/persetujuan

EME	EN 60947-5-2
MTTF [ANN]	629


Data teknis

Berat [g]	125.1
Casing	tipe berulir
Dimensi [mm]	M18 x 1 / L = 80.4
Penamaan ulir	M18 x 1

**Transmitter sensor sinar tembus**

OGS-00KG/2M

Material	baja tahan karat (1.4404 / 316L); PA; EPDM	
Material lensa	PMMA	
Elemen display/pengoperasian		
Display	operasi	1 x LED, hijau
Aksesori		
Item dikirim	mur pengunci: 2	
Keterangan		
Keterangan	tegangan pengoperasian "kelas suplai 2" menurut cULus	
Jumlah paket	1 buah	
Koneksi listrik		
Kabel: 2 m, PUR; 3 x 0.34 mm²		
Koneksi		



BN = Warna core :
BU = coklat
 biru