


Transmitter sensor sinar tembus

OGS-00KG/US100



Karakteristik produk

Tipe cahaya	cahaya merah
Casing	tipe berulir

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	15
Kelas perlindungan	II
Pelindung polaritas terbalik	ya
Tipe cahaya	cahaya merah
Panjang gelombang [nm]	624

Zona pendeteksian

Transmitter/receiver	transmitter
Jarak jangkauan [m]	< 20
Jangkauan yang dapat disesuaikan	tidak
Diameter titik cahaya maks. [mm]	800
Dimensi titik cahaya mengacu pada	pada jangkauan maksimum

Kondisi pengoperasian

Suhu sekitar [°C]	-25...60
Perlindungan	IP 67

Pengujian/persetujuan

EME	EN 60947-5-2
MTTF [ANN]	755

Data teknis

Berat [g]	49.1
Casing	tipe berulir
Dimensi [mm]	M18 x 1 / L = 60


**Transmitter sensor sinar tembus**

OGS-OOKG/US100

Penamaan ulir	M18 x 1		
Material	casing: baja tahan karat (1.4404 / 316L)		
Material lensa	PMMA		
Elemen display/pengoperasian			
Display	operasi	1 x LED, hijau	
Aksesori			
Item dikirim	mur pengunci: 2		
Keterangan			
Keterangan	tegangan pengoperasian "kelas suplai 2" menurut cULus		
Jumlah paket	1 buah		

Koneksi listrik

Konektor: 1 x M12; pengkodean: A

**Koneksi**

Transmitter sensor sinar tembus

OGS-00KG/US100

Diagram dan grafik

grafik excess gain

