

Transmitter sensor sinar tembus

OFS-00KG



Karakteristik produk

Tipe cahaya	cahaya inframerah
Casing	tipe berulir

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	< 20
Kelas perlindungan	II
Pelindung polaritas terbalik	ya
Tipe cahaya	cahaya inframerah
Panjang gelombang [nm]	880

Output

Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian

Transmitter/receiver	transmitter
Jarak jangkauan [m]	< 4
Diameter titik cahaya maks. [mm]	700
Dimensi titik cahaya mengacu pada	pada jangkauan maksimum

Kondisi pengoperasian

Suhu sekitar [°C]	-25...60
Perlindungan	IP 67

Pengujian/persetujuan

EME	EN 60947-5-2
MTTF [ANN]	1597

Data teknis

Berat [g]	72.3
Casing	tipe berulir
Dimensi [mm]	M12 x 1 / L = 60

OF5018



Transmitter sensor sinar tembus

OFS-00KG

Penamaan ulir	M12 x 1
Material	kuningan berlapis nikel
Material lensa	PMMA

Elemen display/pengoperasian

Display	operasi	1 x LED, hijau
---------	---------	----------------

Aksesori

Item dikirim	mur pengunci: 2
--------------	-----------------


Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Kabel: 2 m, PUR; 2 x 0.34 mm²

Koneksi



BN = Warna core :
BU = coklat
 biru