


Sensor refleksi difus

OGT-HPKG/US-100-DPS

Produk tidak tersedia - entri arsip



Karakteristik produk

Tipe cahaya	cahaya inframerah
Casing	tipe berulir

Aplikasi

Prinsip fungsi	Sensor refleksi difus
----------------	-----------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...50 DC
Konsumsi arus [mA]	< 30
Kelas perlindungan	II
Pelindung polaritas terbalik	ya
Tipe cahaya	cahaya inframerah
Panjang gelombang [nm]	880

Output

Desain kelistrikan	PNP
Fungsi output	mode light-on
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	160
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya



Sensor refleksi difus

OGT-HPKG/US-100-DPS

Zona pendeteksian		
Jarak jangkauan	[mm]	2...200; (kertas putih 200 x 200 mm)
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 65
Data teknis		
Casing		tipe berulir
Dimensi	[mm]	M18 x 1
Penamaan ulir		M18 x 1
Material		kuningan berlapis nikel
Material lensa		kaca
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		mur pengunci: 2
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		

Konektor: 1 x M12; pengkodean: A



Koneksi

