


Transmitter sensor sinar tembus

OGS-OOKG/US/90°



Karakteristik produk

Tipe cahaya	cahaya merah
Casing	tipe berulir

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC; ("kelas suplai 2" menurut cULus)
Konsumsi arus [mA]	< 19
Kelas perlindungan	II
Pelindung polaritas terbalik	ya
Tipe cahaya	cahaya merah
Panjang gelombang [nm]	660

Zona pendeteksian

Transmitter/receiver	transmitter
Jarak jangkauan [m]	< 9
Jangkauan yang dapat disesuaikan	tidak
Diameter titik cahaya maks. [mm]	3000
Dimensi titik cahaya mengacu pada	pada jangkauan maksimum

Kondisi pengoperasian

Suhu sekitar [°C]	-25...60
Perlindungan	IP 68

Pengujian/persetujuan

EME	EN 60947-5-2	
	EN 55011	kelas B
MTTF [ANN]		1714

Transmitter sensor sinar tembus

OGS-00KG/US/90°

Data teknis		
Berat	[g]	58
Casing		tipe berulir
Dimensi	[mm]	M18 x 1 / L = 59.3
Penamaan ulir		M18 x 1
Material		baja tahan karat; ABS
Material lensa		PMMA

Elemen display/pengoperasian		
Display	operasi	1 x LED, hijau

Aksesori		
Item dikirim		Mur: 2
		washer pengunci: 2

Keterangan	
Jumlah paket	1 buah

Koneksi listrik

Konektor: 1 x M12; pengkodean: A



Koneksi

