




Receiver sensor sinar tembus

OJE-FPKG/SO/AS



1 tombol tekan



Karakteristik produk		
Tipe cahaya		cahaya merah
Casing		persegi panjang
Aplikasi		
Prinsip fungsi		Sensor sinar tembus
Data kelistrikan		
Tegangan pengoperasian	[V]	10...30 DC
Konsumsi arus	[mA]	< 12
Kelas perlindungan		III
Pelindung polaritas terbalik		ya
Tipe cahaya		cahaya merah
Panjang gelombang	[nm]	660
Output		
Desain kelistrikan		PNP
Fungsi output		mode light-on/dark-on; (dapat diprogram)
Penurunan tegangan maks. pada output peralihan DC	[V]	2.5



Receiver sensor sinar tembus

OJE-FPKG/SO/AS

Peringkat arus permanen dari output peralihan DC [mA]	200
Frekuensi peralihan DC [Hz]	1200
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian

Transmitter/receiver	receiver
Jarak jangkauan [m]	< 10
Jangkauan yang dapat disesuaikan	ya

Kondisi pengoperasian

Suhu sekitar [°C]	-25...60
Perlindungan	IP 67

Pengujian/persetujuan

EME	EN 60947-5-2
MTTF [ANN]	952

Data teknis

Berat [g]	26.8
Casing	persegi panjang
Dimensi [mm]	35 x 11 x 24
Material	casing: ABS; perlengkapan: seng tuang; Jendela LED: SEPS; tombol tekan: SEPS
Material lensa	kaca
Penyelarasan lensa	lensa samping

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
	operasi	1 x LED, hijau
	fungsi	1 x LED, merah
Kunci elektronik	ya	

Aksesori

Item dikirim	Klip dasar: 1, E20964
	sekrup: 2 x M3 x 16
	Washer pegas: 2
	Mur: 2

Keterangan


Keterangan	tegangan pengoperasian "kelas suplai 2" menurut cULus
Jumlah paket	1 buah

Receiver sensor sinar tembus

OJE-FPKG/SO/AS

Koneksi listrik

Konektor: 1 x M8; pengkodean: A

**Koneksi**

2

Teach



Receiver sensor sinar tembus

OJE-FPKG/SO/AS

Diagram dan grafik

grafik excess gain

