


Receiver sensor sinar tembus

OGE-HPKG/US/90°



Karakteristik produk

Tipe cahaya	cahaya merah
Casing	tipe berulir

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC; ("kelas suplai 2" menurut cULus)
Konsumsi arus [mA]	< 12
Kelas perlindungan	II
Pelindung polaritas terbalik	ya
Tipe cahaya	cahaya merah
Panjang gelombang [nm]	660

Output

Desain kelistrikan	PNP
Fungsi output	mode light-on
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	200
Frekuensi peralihan DC [Hz]	500
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian

Transmitter/receiver	receiver
Jarak jangkauan [m]	< 9
Jangkauan yang dapat disesuaikan	tidak



Receiver sensor sinar tembus

OGE-HPKG/US/90°

Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...60
Perlindungan		IP 68
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
MTTF	[ANN]	953
Data teknis		
Berat	[g]	58.7
Casing		tipe berulir
Dimensi	[mm]	M18 x 1 / L = 59.3
Penamaan ulir		M18 x 1
Material		baja tahan karat; ABS
Material lensa		PMMA
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
	operasi	1 x LED, hijau
Aksesori		
Item dikirim		Mur: 2
		washer pengunci: 2
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Konektor: 1 x M12; pengkodean: A		



Koneksi

