


Receiver sensor sinar tembus

OSE-FPKG



Karakteristik produk

Tipe cahaya	cahaya inframerah
Casing	persegi panjang

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...55 DC
Konsumsi arus [mA]	20; ((24 V))
Kelas perlindungan	II
Pelindung polaritas terbalik	ya
Tipe cahaya	cahaya inframerah
Panjang gelombang [nm]	880

Output

Desain kelistrikan	PNP
Fungsi output	mode light-on/dark-on; (dapat diprogram)
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	100
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya



Receiver sensor sinar tembus

OSE-FPKG

Zona pendeteksian		
Transmitter/receiver		receiver
Jarak jangkauan [m]		< 20
Jangkauan yang dapat disesuaikan		ya
Kondisi pengoperasian		
Suhu sekitar [°C]		-25...80
Perlindungan		IP 65
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
MTTF [ANN]		618
Data teknis		
Berat [g]		274.5
Casing		persegi panjang
Dimensi [mm]		80 x 28 x 95
Material		PPO dimodifikasi
Material lensa		kaca
Penyelarasan lensa		lensa samping
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		Braket siku: 1, E20210
		obeng
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
terminal: ...1.5 mm ² ; Konektor kabel: M20 X 1.5		
Koneksi		

