


Transmitter sensor sinar tembus

OTS-00KG/US-100



masing-masing satu dioda transmisi di lensa atas dan bawah



Karakteristik produk

Tipe cahaya	cahaya inframerah
Casing	persegi panjang

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...50 DC
Konsumsi arus [mA]	20; ((24 V))
Kelas perlindungan	II
Pelindung polaritas terbalik	ya
Tipe cahaya	cahaya inframerah
Panjang gelombang [nm]	880

Zona pendeteksian

Transmitter/receiver	transmitter
Jarak jangkauan [m]	< 10
Jangkauan yang dapat disesuaikan	tidak
Diameter titik cahaya maks. [mm]	524
Dimensi titik cahaya mengacu pada	pada jangkauan maksimum

Kondisi pengoperasian

Suhu sekitar [°C]	-25...60
-------------------	----------



Transmitter sensor sinar tembus

OTS-00KG/US-100

Perlindungan	IP 65
--------------	-------

Pengujian/persetujuan

EME	EN 60947-5-2	
	EN 55011	kelas B
MTTF [ANN]	1862	

Data teknis

Berat [g]	153
Casing	persegi panjang
Material	PBT
Material lensa	PMMA
Penyelarasan lensa	lensa samping

Elemen display/pengoperasian

Display	operasi	1 x LED, hijau
---------	---------	----------------

Aksesori

Item dikirim	Braket siku: 1, E20461 obeng
--------------	---------------------------------

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Konektor: 1 x M12; pengkodean: A



Koneksi

