


Receiver sensor sinar tembus

OUE-DPKG/US-100-DPS



receiver di lensa atas



Karakteristik produk

Tipe cahaya	cahaya inframerah
Casing	persegi panjang

Aplikasi

Prinsip fungsi	Sensor sinar tembus
----------------	---------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...55 DC
Konsumsi arus [mA]	20; ((24 V))
Kelas perlindungan	III
Pelindung polaritas terbalik	ya
Tipe cahaya	cahaya inframerah
Panjang gelombang [nm]	880

Output

Desain kelistrikan	PNP
Fungsi output	mode dark-on
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	140
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya


Zona pendeteksian

Transmitter/receiver	receiver
Jarak jangkauan [m]	< 6
Jangkauan yang dapat disesuaikan	ya



Receiver sensor sinar tembus

OUE-DPKG/US-100-DPS

Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 60947-5-2	
MTTF	[ANN]	618
Data teknis		
Berat	[g]	73
Casing		persegi panjang
Dimensi	[mm]	28 x 16 x 51
Material		PPO dimodifikasi
Material lensa		kaca
Penyelarasan lensa		lensa samping
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		Braket siku: 1, E20211
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Konektor: 1 x M12; pengkodean: A		
		
Koneksi		
		

Receiver sensor sinar tembus

OUE-DPKG/US-100-DPS

Diagram dan grafik

grafik excess gain

