


Sensor refleksi difus

OTT-FPKG/US-100-IPF

Produk tidak tersedia - entri arsip



receiver di lensa bawah
transmitter di lensa atas

Karakteristik produk

Tipe cahaya	cahaya inframerah
Casing	persegi panjang

Aplikasi

Prinsip fungsi	Sensor refleksi difus
----------------	-----------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...50 DC
Konsumsi arus [mA]	40; ((24 V))
Kelas perlindungan	II
Pelindung polaritas terbalik	ya
Tipe cahaya	cahaya inframerah
Panjang gelombang [nm]	880

Output

Desain kelistrikan	PNP
Fungsi output	mode light-on/dark-on; (dapat ditentukan parameternya)
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	150
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa



Sensor refleksi difus

OTT-FPKG/US-100-IPF

Pelindung beban berlebih	ya	
Zona pendeteksian		
Jarak jangkauan [mm]	10...40; (kertas putih 200 x 200 mm)	
Jangkauan yang dapat disesuaikan	ya	
Kondisi pengoperasian		
Suhu sekitar [°C]	-25...60	
Perlindungan	IP 65	
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing	persegi panjang	
Dimensi [mm]	75 x 19 x 30	
Material	PBT	
Material lensa	PMMA	
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
	operasi	1 x LED, hijau
Aksesori		
Item dikirim	Braket siku obeng	
Keterangan		
Jumlah paket	1 buah	
Koneksi listrik		
Konektor: 1 x M12; pengkodean: A		
		



Sensor refleksi difus

OTT-FPKG/US-100-IPF

Koneksi

