


Encoder inkremental dengan poros solid

RB-0060-I24/S

Produk tidak tersedia - entri arsip



- 1 tanda referensi
2 M3 kedalaman 5 mm



Karakteristik produk

Resolusi	60 resolusi
Desain poros	poros solid
Diameter poros [mm]	6

Aplikasi

Fitur khusus	Bebas halogen
--------------	---------------

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	150

Output

Desain kelistrikan	HTL
Beban arus maks. per output [mA]	50
Frekuensi peralihan [kHz]	160
Tipe pelindung hubung singkat	< 60 s
Perbedaan fase A dan B [°]	90

Rentang pengukuran/pengaturan

Resolusi	60 resolusi
----------	-------------

Kondisi pengoperasian

Suhu sekitar [°C]	-20...70
Suhu penyimpanan [°C]	-30...100
Kelembapan udara relatif maks. [%]	98
Perlindungan	IP 64

Pengujian/persetujuan

Tahan guncangan	100 g (6 ms)
Ketahanan terhadap getaran	10 g (55...2000 Hz)



Encoder inkremental dengan poros solid


RB-0060-I24/S

Data teknis		
Dimensi	[mm]	Ø 36.5 / L = 38
Material		aluminium
Putaran maks., mekanis	[U/min]	10000
Torsi awal maks.	[Nm]	1
Torsi suhu referensi	[°C]	20
Desain poros		poros solid
Diameter poros	[mm]	6
Material poros		baja (1.4104)
Beban poros aksial maks. (di ujung poros)	[N]	5
Beban poros radial maks. (di ujung poros)	[N]	10

Koneksi listrik

Kabel: 0.3 m, PUR, Bebas halogen


Konektor: 1 x M23 (ifm 1001.6)



1	0V B
2	n.c.
3	indeks 0
4	0V indeks 0
5	A
6	0V A
7	kegagalan dibalik
8	B
9	n.c.
10	0V
11	n.c.
12	10...30V
Penutup	casing

Diagram dan grafik

Diagram pulsa



arah putaran searah jarum jam (menghadap poros)