



Encoder multiturn absolut dengan poros solid

RMU Profibus

Software/pemrograman		
Opsi pengaturan parameter	arah penghitungan nilai kode; Resolusi; titik nol; switch batas HI dan LO; indikator gerakan; multiturn/singleturn	
Fungsi diagnostik	alarm; peringatan; status; nomor seri encoder	
Alamat	switch pemilih alamat; 0...126	
Interface		
Interface komunikasi	PROFIBUS DP	
PROFIBUS DP		
Standar transmisi	DPV0 Class 2 (EN50170)	
Laju transmisi	...12 Mbit/s	
Kondisi pengoperasian		
Suhu sekitar	[°C]	-40...70
Perlindungan	IP 66; (pada casing: IP 67; pada poros: IP 66)	
Pengujian/persetujuan		
Tahan guncangan		100 g (6 ms)
Ketahanan terhadap getaran		10 g (55...2000 Hz)
Data teknis		
Berat	[g]	652
Dimensi	[mm]	Ø 58 / L = 90.5
Material		aluminium
Putaran maks., mekanis	[U/min]	12000
Torsi awal maks.	[Nm]	1
Torsi suhu referensi	[°C]	20
Desain poros		poros solid
Diameter poros	[mm]	6
Material poros		baja (1.4104)
Beban poros aksial maks. (di ujung poros)	[N]	10
Beban poros radial maks. (di ujung poros)	[N]	20
Flensa pemasangan		flensa sinkronisasi
Koneksi listrik		
strip terminal pada ruang terminal: ; Panjang kabel maksimal: 100 m; 400 m (1.5 Mb/s)		